




Known for Reliability Since 1921

Increase your product yield and make tasty, flavorable, value-added products with the BIRO Model VTS-100 or Model VTS-500 Vacuum Tumblers. Both Tumblers have a 3/4 HP vacuum pump motor that can evacuate the drum chamber quickly. The three stage timer on the VTS-500 lets you program relax time into your tumbling cycle for products such as hams or bellies. The Run/jog controls let you position the drum for easy cleaning or unloading. Heavy duty casters let you do your tumbling virtually anywhere in your plant. The drain hole in the drum makes cleanup a snap. Improve your profit margin with value-added products from the BIRO VTS-100 or the VTS-500 Vacuum Marinating Tumblers.






Optional- VTS-100/500 Quick Access Hinged (water-protected) Control Panel Cover -Recommended in water jet wash environments.



MODEL SPECIFICATIONS



									—			
Models		VTS-100 Vacuum Marinating Tumbler							VTS-500 Vacuum Marinating Tumbler			
Electrical	115 Volts, 60 Cycle, 1 Phase has 8' Cord and Plug; 220Volts, 50/60 Cycle, 1 Phase has 8' Cord, No Plug.											
Construction	Stainless steel drum and frame.											
Motors	Co	Controls are NEMA 4X rated										
		MOTOR	HP	TYPE	KW	VOLTS	AMPS	HERTZ	PH	CODE	EC = Extra Cost	
		DRIVE	3/4	TEFC	.56	115/230	12/6	60	1	STD	STD = Standard OPDP = Open Drip Proof	
	1 -	PUMP	3/4	OPDP	.56	115/230	12/6	60	1	STD	TEFC = Totally Enclosed Fan Cooled	
		DRIVE PUMP	3/ ₄ 3/ ₄	TEFC OPDP	.56 .56	220 220	7.6 5.0	50 50	1	EC EC]	
Drum		100 lbs. (45.4 kg) Maximum 500 lbs. (227 kg) Maximum										
Capacity	100 lbs. (45.4 kg) Approximate, Optimum tumbling load.								440 lbs. (199 kg) Approximate, Optimum tumbling load.			
Dump Height Less Lid	30" (762mm), Drum opening at 9 O'clock position. 24" (609mm), Drum opening at 9 O'clock position.											
		25.75" (654mm), Drum opening at 6 O'clock position. 21.125" (536.6mm), Drum opening at 6 O'clock position										
Drive Motor		³ / ₄ HP (.56kw) DC, Variable speed (0-14 RPM), 60:1 Transmission, TEFC (Totally Enclosed Fan Cooled).										
Vacuum Pump		³ / ₄ HP (.56kw), 60 cycle, 1 phase - 10 CFM - Rotary vane type										
Timer	0-50 Minute, Interval mode timer (dial). 0-999 Min., Programmable multi-function timer w/ Time in										able multi-function timer w/ Time inhibit.	
Tumble Speed	0 - 14 RPM											
Safety Standard		Photoelectric eye, for safety shut down.										
Standard	5" Locking swivel casters • Drain cap wrench • External moisture trap with removal tool • Internal in-line vacuum f									• Internal in-line vacuum filter • 1 Extra		
Features		filter element • 8' cord and plug 115V • 8' cord NO plug 220V • 4 Quick release toggle clamps on lid •										
	Silicone lid gasket • Operating and Safety manual.											
Options (EC)	220-50-1 or 230-60-1 • Leg extensions • Stainless steel swivel								220-50-1 or 230-60-1 • Leg extensions • Stainless steel swivel			
options (20)	locking (delrin bearing) casters with stainless steel (swivel plate)								locking (delrin bearing) casters with stainless steel (swivel plate)			
	ball bearings • Reverse switch momentary • Programmable							bal	ball bearings • Reverse switch momentary • Stainless steel			
	multi-function timer • Stainless steel crimped fittings on hose							crimp	crimped fittings on hose • Protective enclosure for control panel.			
	Protective enclosure for control panel.											
Certifications		N.S.F.							U.L. (115V - 60 Hz Only) & N.S.F.			
Weight		Uncrated: 468 lbs. (212 kg) Approximate							Uncrated: 645 lbs. (293 kg) Approximate			
D'		Crated: 711 lbs. (323 kg) Approximate							Crated: 990 lbs. (449 kg) Approximate			
Dimensions Crated	L	L = 72" (1829mm) x W = 42" (1067mm) x H = 53" (1346mm). $L = 96$ " (2438mm) x W = 42" (1067mm) x H = 57" (1448mm)										
Allowable		A rec	quired m	inimum	distance	of 12" from b	ack of mad	hine to ne	earest o	bject must	be maintained for rotating drum.	
Workspace										,		

BIRO MANUFACTURING COMPANY 1114 WEST MAIN STREET MARBLEHEAD, OH 43440-2099 U.S.A.

Phone: (419) 798-4451 • Fax: (419) 798-9106

www.birosaw.com • sales@birosaw.com

ITEM NO.: LIT-VTS-100/500-328 FORM NO.: Md VTS-100/500-328-1-21-5