

# GVS Nailstation - 4 Zone Extraction for Complete Protection

### Adjustable Arm

Evaporating solvent and chemical fumes are safely captured by an adjustable stainless steel arm with integrated work lamp.

#### Downdraught Disc

A downdraught system pulls the nail dust down into the filter through a removable grill and away from your breathing zone.

#### Plenum Cowl

Open containers can release fumes into the air. This is prevented by a plenum cowl positioned on the worktop.

#### Vented Drawer

Fumes are extracted from the rear of the drawer. This ensures fumes are not released when the drawer is opened.



Voltage: 220-240 50Hz (Optional US Market - 120v 50/60Hz) Fan motor: Low noise radial type ,140W Air flow: 25cbm/hour Fan control: Variable Cabinet and bench top: Solvent resistant P.U. coated MDF Hinges and runners: Blum 'soft close' hinges and drawer runners Lamp arm: Spiral wound stainless steel Lamp shade: Brushed finish stainless steel Main Extraction Grill: Laser cut stainless steel Handles: Stainless steel, brushed finish Bulb: 12v GU5.3 50W 3000k (Optional 8W LED 3000k) Cowl: Clear Polycarbonate Power lead: 2m cord with UK / EU / US plug

#### Guarantee: 2 Years

Filter Life\* Pre Filter: 3 months Carbon:12-18 months

\* In normal operating conditions



Type: 1.5 Rectangle





## Colours



## **Key Benefits**

Pre-filter element removes dust and airborne particles

Activated carbon filter removes solvents and fumes

 Reduces the risk of health compensation claims from employees and ensures that salon owners comply with Health and Safety leaislation

- Reduces the risk of clients breathing harmful dust and fumes
- Ensures dust and odour free salon giving a competitive advantage over other salons
- Operates quietly and efficiently and has excellent filter life to
  ensure low running costs

Allows customers to offer new treatments in areas where
noxious odours would not be tolerated



