

GVS Nailstation - 4 Zone Extraction for Complete Protection

Adjustable Arm

Evaporating solvent and chemical fumes are safely captured by an adjustable stainless steel arm with integrated work lamp.

Downdraught Disc

A downdraught system pulls the nail dust down into the filter through a removable grill and away from your breathing zone.


Plenum Cowl

Open containers can release fumes into the air. This is prevented by a plenum cowl positioned on the worktop.

Vented Drawer

Fumes are extracted from the rear of the drawer. This ensures fumes are not released when the drawer is opened.

Type: 1.2 Kidney



Specification

Voltage: 220-240 50Hz (Optional US Market - 120v 50/60Hz)

Fan motor: Low noise radial type ,140W

Air flow: 25cbm/hour

Fan control: Variable

Cabinet and bench top: Solvent resistant P.U. coated MDF

Hinges and runners: Blum 'soft close' hinges and drawer runners

Lamp arm: Spiral wound stainless steel

Lamp shade: Brushed finish stainless steel

Main Extraction Grill: Laser cut stainless steel

Handles: Stainless steel, brushed finish

Bulb: 12v GU5.3 50W 3000k (Optional 8W LED 3000k)

Cowl: Clear Polycarbonate

Power lead: 2m cord with UK / EU / US plug




Guarantee: 2 Years

Filter Life*

Pre Filter: 3 months

Carbon: 12-18 months

** In normal operating conditions*



Colours



Black

Light Oak

Walnut

White

Key Benefits

- Pre-filter element removes dust and airborne particles
- Activated carbon filter removes solvents and fumes
- Reduces the risk of health compensation claims from employees and ensures that salon owners comply with Health and Safety legislation
- Reduces the risk of clients breathing harmful dust and fumes
- Ensures dust and odour free salon giving a competitive advantage over other salons
- Operates quietly and efficiently and has excellent filter life to ensure low running costs
- Allows customers to offer new treatments in areas where noxious odours would not be tolerated