

Resinex™ K-8 UB H

Strong acid cation resin

Resinex™ K-8 UB H is a strongly acidic gel-type cation exchange resin. The crosslinked, polystyrene divinylbenzene matrix provides excellent resistance to physical breakdown. The high capacity achieved in demineralisation makes it suitable for most standard industrial water treatment applications. Together with the optimisation of regenerant consumption, **Resinex™ K-8 UB H** will allow you to obtain a high quality process water in economical manner.

The selected bead distribution - very close to monospheric - is especially adapted for all modern systems (UPCORE, Schwebebett,...) and mixed bed systems.

Typical Properties

Type	Crosslinked polystyrene divinylbenzene
Form	Gel-type, amber, spherical beads
Functional group	Sulfonic acid
Whole bead count	95% min.
Ionic form, as shipped	H ⁺
Bead size	(≥ 90%) 0.50 - 0.71 mm
Uniformity coefficient	1.20 max.
Bulk density, as shipped	820 kg/m ³
Real density	1.22 g/cm ³
Water retention	48 - 55%
Total capacity (H ⁺ form)	1.90 eq/l min.
Volume change Na ⁺ → H ⁺	8% max.
Stability, temperature	120°C max.
Stability, pH	0 - 14

Standard Design Conditions

Bed depth	> 700 mm
Service flow rate	8 - 55 BV/h
Backwash expansion	50 - 75%

Key Features and Benefits

- **High Integrity Beads**
Excellent resistance to mechanical degradation ensures low pressure drop
- **Extended Operating Capacity**
Economical advantage
- **European ResAP (2004) 3 Approved**
Meets European Council Resolution AP (2004) 3 for use of ion exchange resins in processing of food products
- **WRAS BS 6920 Approved**
BS 6920 for cold water and hot water up to 85°C
- **Uniform Bead Size**
Lower pressure drop and regenerant consumption
- **Perfect Separation**
Suitable for Mixed-bed applications

Typical Applications

- Industrial Softening
- Demineralisation in industrial water treatment systems together with **Resinex™ A-4 UB**
- Polishing Mixed-bed systems together with **Resinex™ A-4 UB OH**

Standard Packaging

- 25 lit. PE valve bag
- 1000 litre big bag



This product has been tested and certified to NSF/ANSI Standard 44 for materials safety only.

A minimum flow of 0.39 gpm per cubic foot of media is required.




TRADEMARK OF JACOBI CARBONS. WWW.JACOBI.NET

Resinex™
Ion Exchange Resin


Resinex™ K-8 UB H

Strong acid cation resin

Pressure Drop



Backwash Expansion



Standard Regeneration Parameters for Softening

Regeneration	Co-Flow	Counter-Flow
Concentration	10% NaCl	10% NaCl
Level	80-300 g/l	50-150 g/l
Flow rate regeneration	4-6 BV/h	5-8 BV/h
Contact time regeneration	30-60 min.	20-40 min.
Flow rate rinse	5-20 BV/h	5-20 BV/h
Rinse water required	8-15 BV	3-6 BV

Standard regeneration Parameters for Demineralisation

Regeneration	Co-Flow	Counter-Flow
Concentration	8% HCl	5% HCl
Level	60-150 g/l	45-70 g/l
Flow rate regenerant	4-6 BV/h	5-8 BV/h
Contact time regeneration	30-60 min.	20-40 min.
Flow rate slow rinse	5-20 BV/h	5-20 BV/h
Slow rinse water required	8-15 BV	3-6 BV
Flow rate fast rinse	20-40 BV/h	20-40 BV/h
Fast rinse water required	8-15 BV	3-6 BV

Product Packing



25 lit. polyethylene valve bag
48 bags per pallet



Polypropylene FIBCs
(big bag), 1.000 lit.



NOTICE Jacobi Carbons reserves the right to change product specifications without prior notification. The information contained in this datasheet is intended to assist a customer in the evaluation and selection of products supplied by Jacobi Carbons. The customer is responsible for determining whether products and the information contained in this document are appropriate for the customers use. Jacobi Carbons assumes no obligation or liability for the usage of the information in this datasheet, no guarantees or warranties, expressed or implied, are provided. Jacobi Carbons disclaims responsibility and the user must accept full responsibility for performance of systems based on this data.

CAUTION Strong oxidizing agents such as nitric acid can react violently with ion exchange resins and cause explosive type reactions. Before using strong oxidants, consult sources knowledgeable in the handling of these materials.



SWEDEN

Jacobi Carbons AB
Vanvsholmen
SE-392 30 Kalmar
Phone: +46-480-417550
FAX: +46-480-417559
Email: info@jacobi.net

FINLAND

Jacobi Carbons AB (SS)
Ruoholahdenkatu 8
SF-00180 Helsinki
Phone: +358-9-643602
FAX: +358-9-642900
Email: infofin@jacobi.net

GERMANY

Jacobi Carbons GmbH
Feldbergstraße 21
D-60323 Frankfurt/Main
Phone: +49-69-719107-0
FAX: +49-69-719107-20
Email: infode@jacobi.net

UNITED STATES

Jacobi Carbons, Inc.
1335 Dublin Road Suite 217D
Columbus, OH 43215
Phone: +1-215-546-3900
FAX: +1-215-546-9921
Email: infous@jacobi.net

UNITED KINGDOM

Jacobi Carbons Ltd
E12 Croft Court, Moss Estate
WN73PT Leigh, Lancashire
Phone: +44-1942-670600
FAX: +44-1942-670605
Email: infouk@jacobi.net

MALAYSIA

Jacobi Carbons (Asia) Sdn Bhd
Lot 12070-F, Jalan Usahajaya,
Permatang Tinggi, 14100, Penang
Phone: +60-4-5882122
FAX: +60-4-5886122
Email: infoasia@jacobi.net



Jacobi

www.resinex-ixr.com
www.jacobi.net